

Vacuum pump

EVE-OG 40 AC3




Art.-Nr.: 10.03.02.00072



EVE-OG 40 AC3

Technical data

Attribute	Value
Rated power at 50 Hz	1.10 kW
Voltage at 50 Hz	200 - 240 V or 345 - 420 V
Suction rate (50 Hz)	40.000 m ³ /h
Current type	Three phase A.C.



Design data EVE-OG 40 AC3

Design data

Attribute	Value
Thread G3	G1-1/4"-F



WWW.SCHMALZ.COM/10.03.02.00072

Art.-Nr.: 10.03.02.00072

**Technical data**

Attribute	Value
Protection type IP	IP 54
Max. vacuum	-980 mbar
Rated power at 50 Hz	1.10 kW
Voltage 50 Hz	S003
Voltage at 50 Hz	200 - 240 V or 345 - 420 V
Suction rate (50 Hz)	40.000 m ³ /h
Suction rate -800	40.0 m ³ /h
Current range (50 Hz)	4.8 A or 2.8 A
Current type	Three phase A.C.

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00072