

Art.-Nr.: 10.03.02.00112



EVE-OG 21 AC3

Technical data

Attribute	Value
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	230 / 400 V AC3
Suction rate (50 Hz)	21.000 m ³ /h
Suction rate (60 Hz)	27.000 m ³ /h
Length L	320.50 mm
Current type	Three phase A.C.

Design data

Attribute	Value
Length L	320.50 mm
Width B	227.00 mm
Height H	182.00 mm
Thread G2	G3/4"-F
Thread G5	M6-F

Design data EVE-OG 21 AC3

**Technical data**

Attribute	Value
Protection type IP	IP 55
Max. vacuum	-980 mbar
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage 50 Hz	230/400AC3
Voltage at 50 Hz	230 / 400 V AC3
Suction rate (50 Hz)	21.000 m ³ /h
Suction rate -800	21.0 m ³ /h
Current type	Three phase A.C.



Vacuum pump

EVE-OG 21 AC3



Art.-Nr.: 10.03.02.00112



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00112



WWW.SCHMALZ.COM/10.03.02.00112