



Art.-Nr.: 10.03.02.00076



EVE-OG 63 AC3 AQUA IE2

Technical data

Attribute	Value
Rated power at 50 Hz	2.00 kW
Rated power at 60 Hz	2.40 kW
Voltage at 50 Hz	190-208 V / 380 - 415 V AC3
Voltage at 60 Hz	220 - 230 V / 440 - 480 V AC3
Suction rate (50 Hz)	63.000 m ³ /h
Length L	626.00 mm
Current type	Three phase A.C.



Design data EVE-OG 63 AC3 AQUA IE2

Design data

Attribute	Value
Length L	626.00 mm
Width B	407.00 mm
Height H	290.00 mm
Thread G3	G1-1/4"-F
Thread G5	M8-F

Art.-Nr.: 10.03.02.00076

**Technical data**

Attribute	Value
Protection type IP	IP 55
Max. vacuum	-980 mbar
Rated power at 50 Hz	2.00 kW
Rated power at 60 Hz	2.40 kW
Voltage 50 Hz	S052
Voltage at 50 Hz	190-208 V / 380 - 415 V AC3
Voltage at 60 Hz	220 - 230 V / 440 - 480 V AC3
Suction rate (50 Hz)	63.000 m ³ /h
Suction rate -800	63.0 m ³ /h
Voltage 60 Hz	S053
Current type	Three phase A.C.
Type	AQUA

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00076**Ordering Data Accessories 10.03.02.00076**

Typ		Artikelnummer
Filter insert (round)	FILT-EINS PES EVE-Apua	10.07.01.00376
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055

