

Art.-Nr.: 10.03.04.00119

**Technical data**


Attribute	Value
Reservoir volume	50.0 l
Suction rate -800	25.0 m ³ /h
Voltage	230/400V ±10%
with	regulated engine circuit

VZ-TR 25 AC3 50 GMS

Vacuum centre VZ is delivered as a ready to connect product.

Available spare parts: replacement cartridge for air cleaner, replacement cartridge for oil filter

Available accessories: filter cartridge for vacuum reservoir

**Design data**

Attribute	Value
Length L1	730.00 mm
Length L	710.00 mm
Width B1	630.00 mm
Width B	510.00 mm
Height H	580.00 mm
Internal diameter d	11.00 mm
Thread G2	G1-1/4"-F
Hole spacing Y1	470.0 mm
Hole spacing X1	480.0 mm

Design data VZ-TR 25 AC3 50 GMS

Art.-Nr.: 10.03.04.00119

**Technical data**

Attribute	Value
Protection type IP	IP 44
Max. vacuum	-25.100 inHg
Motor power	0.75 kW
Weight	71.000 kg
Reservoir volume	50.0 l
Suction rate -800	25.0 m³/h
Product family	VZ
Voltage	230/400V ±10%

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.04.00119**Ordering Data Spare Parts 10.03.04.00119**

Typ		Item number
Filter insert (round)	FILT-EINS EVE-TR-25-40	10.03.01.00023
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

