

Art.-Nr.: 10.03.02.00082



EVE-OG 10 AC3 F


Vacuum pump EVE-OG is delivered as a ready-to-connect product.

Available spare parts: filter cartridge (filter insert), replacement oil, maintenance kit (set of parts subject to wear pump)

Available accessories: motor-protection switch, filter resistance gauge (pressure manometer)

Technical data

Attribute	Value
Rated power at 50 Hz	0.37 kW
Voltage at 50 Hz	230 / 400 V AC
Voltage at 60 Hz	230 / 400 V AC
Weight	19.000 kg
Suction rate (50 Hz)	10.000 m ³ /h
Suction rate (60 Hz)	12.000 m ³ /h
Sound pressure level at 50 Hz	49.0 dB(A)
Voltage 60 Hz	230/400-AC
Current type	Three phase A.C.
with	Filter



Design data EVE-OG 10 AC3 F


Design data

Attribute	Value
Length L2	63.00 mm
Length L	422.00 mm
Width B2	26.00 mm
Width B	212.00 mm
Height H1	320.00 mm
Height H2	70.00 mm
Height H	211.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	111.0 mm
Hole spacing X1	176.0 mm

Art.-Nr.: 10.03.02.00082

**Technical data**

Attribute	Value
Protection type IP	IP 54
Max. vacuum	-28.939 inHg
Rated power at 50 Hz	0.37 kW
Voltage at 50 Hz	230 / 400 V AC
Weight	19.000 kg
Suction rate (50 Hz)	10.000 m ³ /h
Sound pressure level at 50 Hz	49.0 dB(A)
Product family	EVE-OG
Supply voltage	AC3

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800	1000
EVE-OG 10 50 Hz	10.00	8.00	6.00	3.90	1.85	-
EVE-OG 10 60 Hz	12.00	9.70	7.00	4.80	2.10	-

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.02.00082WWW.SCHMALZ.COM/10.03.02.00082

Vacuum pump

EVE-OG 10 AC3 F



Art.-Nr.: 10.03.02.00082



Ordering Data Accessories 10.03.02.00082

Typ		Item number
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Accessories	ZUB EVE-OG Ölablass-Kit	22.09.03.00038



WWW.SCHMALZ.COM/10.03.02.00082