

Art.-Nr.: 10.03.04.00173

**Technical data**


Attribute	Value
Reservoir volume	15.0 l
Suction rate -800	10.0 m ³ /h
Voltage	230/400V ±10%
with	regulated engine circuit

VZ-TR 10 AC3 15 GMS

Vacuum centre VZ is delivered as a ready to connect product.

Available spare parts: replacement cartridge for air cleaner, replacement cartridge for oil filter

Available accessories: filter cartridge for vacuum reservoir

**Design data**

Attribute	Value
Length L1	430.00 mm
Length L	430.00 mm
Width B1	490.00 mm
Width B	400.00 mm
Height H	440.00 mm
Internal diameter d	11.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	360.0 mm
Hole spacing X1	280.0 mm

Design data VZ-TR 10 AC3 15 GMS



Art.-Nr.: 10.03.04.00173

**Technical data**

Attribute	Value
Protection type IP	IP 44
Max. vacuum	-25.100 inHg
Motor power	0.37 kW
Weight	38.500 kg
Reservoir volume	15.0 l
Suction rate -800	10.0 m³/h
Product family	VZ
Voltage	230/400V ±10%

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.04.00173**Ordering Data Spare Parts 10.03.04.00173**

Typ	Item number
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG 10.07.01.00017

**Ordering Data Wear Parts 10.03.04.00173**

Typ	Item number
Filter insert (round)	FILT-EINS EVE-16-25 10.03.01.00022

