



EVE-WR 65 AC3


Vacuum pump EVE-WR is delivered as a ready to connect product.

Available accessories: additional filter, motor-protection switch

Technical data

Attribute	Value
Rated power at 50 Hz	2.40 kW
Rated power at 60 Hz	2.40 kW
Voltage at 50 Hz	200 - 240 V or 345 - 420 V
Weight	68.000 kg
Suction rate (50 Hz)	65.000 m ³ /h
Sound pressure level at 50 Hz	70.0 dB(A)
Current type	Three phase A.C.

Design data



Attribute	Value
Length L2	85.00 mm
Length L	764.00 mm
Width B	572.00 mm
Height H1	553.00 mm
Height H	436.00 mm
Outside diameter D2	50.0 mm
Internal diameter d	14.00 mm
Hole spacing Y1	495.0 mm
Hole spacing X1	450.0 mm

Design data EVE-WR 65 AC3

Art.-Nr.: 10.03.05.00016

**Technical data**

Attribute	Value
Protection type IP	IP 54
Rated power at 50 Hz	2.40 kW
Rated power at 60 Hz	2.40 kW
Voltage at 50 Hz	200 - 240 V or 345 - 420 V
Voltage at 60 Hz	200 - 275 V or 345 - 480 V
Weight	68.000 kg
Suction rate (50 Hz)	65.000 m ³ /h
Sound pressure level at 50 Hz	70.0 dB(A)
Supply voltage	AC3

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.05.00016**Ordering Data Accessories 10.03.05.00016**

Typ		Item number
Motor-protection switch	MSS-K 8-12A	10.04.04.00123

