

Art.-Nr.: 10.04.01.00121




SB 510 200 4 IE3-TYP1 ER

Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.

Technical data

Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D230 V / Y400 V ±10 %
Voltage at 60 Hz	D265 V / Y460 V ±10 %
Weight	83.000 kg
Suction rate (50 Hz)	510.000 m³/h
Suction rate (60 Hz)	610.000 m³/h
Color	RAL 7035 Light grey
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	200 mbar
Vacuum (60 Hz)	175 mbar
with	Electro-pneumatic reversing
Approval	UL/CSA



Design data

Length L	860.00 mm
Width B1	507.00 mm
Width B	496.00 mm
Height H2	134.00 mm
Height H	573.00 mm
Internal diameter d	13.00 mm
Thread G1	G2-1/2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm

Design data SB 510 200 4 IE3-TYP1 ER

Vacuum blower

SB 510 200 4 IE3-TYP1 ER



Art.-Nr.: 10.04.01.00121



Technical data

Protection type IP	IP 55
Max. vacuum	200 mbar
Rated power at 50 Hz	4.00 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	83.000 kg
Suction rate (50 Hz)	510.000 m ³ /h
Product family	SB-ER
Approval	UL/CSA



WWW.SCHMALZ.COM/10.04.01.00121