

Check valve
SVK M5-IG



Art.-Nr.: 10.05.03.00033



SVK M5-IG


Check valves SVK, SVKG, SVV are delivered as a ready-to-connect product.

Technical data

Attribute	Value
Thread G1	M5-M
Thread G2	M5-F

Design data

Attribute	Value
Length L	15.50 mm
Thread G1	M5-M
Thread length LG1	4.5 mm
Thread G2	M5-F
Thread length LG2	4.5 mm
Key width SW1	8.0 mm



Design data SVK M5-IG



WWW.SCHMALZ.COM/10.05.03.00033

Art.-Nr.: 10.05.03.00033

**Technical data**

Attribute	Value
Weight	2.2 g
Required suction capacity for $p_u = -0.3$ bar	0.070 m ³ /h
Required suction capacity for $p_u = -0.6$ bar	0.080 m ³ /h
Flow rate max.	4.800 m ³ /h
Product family	SVK
Flow rate max. pressure	80.0 l/min

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.03.00033

