


Art.-Nr.: 10.04.01.00148



SB 325 265 3 IE3-TYP1 ER

Vacuum blower SB with electro-pneumatic reversing is delivered as a ready to connect product.



Design data SB 325 265 3 IE3-TYP1 ER

Technical data

Attribute	Value
Rated power at 50 Hz	3.00 kW
Rated power at 60 Hz	3.60 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	78.000 kg
Suction rate (50 Hz)	325.000 m ³ /h
Suction rate (60 Hz)	390.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	265 mbar

Design data

Attribute	Value
Length L	798.00 mm
Width B1	502.00 mm
Width B	439.00 mm
Height H2	134.00 mm
Height H	476.00 mm
Internal diameter d	13.00 mm
Thread G1	G2"-M
Hole spacing Y1	446.0 mm
Hole spacing X1	435.0 mm

Art.-Nr.: 10.04.01.00148



Technical data

Attribute	Value
Protection type IP	IP 55
Max. vacuum	265 mbar
Rated power at 50 Hz	3.00 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	78.000 kg
Suction rate (50 Hz)	325.000 m ³ /h
Product family	SB-ER
Approval	UL/CSA



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00148

