



SVK G3/8-IG


Check valves SVK, SVKG, SVV are delivered as a ready-to-connect product.

Technical data

Attribute	Value
Thread G1	G3/8"-M
Thread G2	G3/8"-F

Design data

Attribute	Value
Length L	29.00 mm
Thread G1	G3/8"-M
Thread length LG1	10.0 mm
Thread G2	G3/8"-F
Thread length LG2	12.0 mm
Key width SW1	22.0 mm



Design data SVK G3/8-IG

Art.-Nr.: 10.05.03.00036

**Technical data**

Attribute	Value
Weight	30.3 g
Required suction capacity for $p_u = -0.3$ bar	0.440 m ³ /h
Required suction capacity for $p_u = -0.6$ bar	0.480 m ³ /h
Flow rate max.	35.400 m ³ /h
Product family	SVK
Flow rate max. pressure	590.0 l/min

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.03.00036

