




SVK G1/8-IG

Check valves SVK, SVKG, SVV are delivered as a ready-to-connect product.

Technical data

Attribute	Value
Thread G1	G1/8"-M
Thread G2	G1/8"-F

Design data



Design data SVK G1/8-IG

Attribute	Value
Length L	26.00 mm
Thread G1	G1/8"-M
Thread length LG1	8.0 mm
Thread G2	G1/8"-F
Thread length LG2	8.5 mm
Key width SW1	14.0 mm

Art.-Nr.: 10.05.03.00034

**Technical data**

Attribute	Value
Weight	11.2 g
Required suction capacity for $p_u = -0.3$ bar	0.140 m ³ /h
Required suction capacity for $p_u = -0.6$ bar	0.150 m ³ /h
Flow rate max.	18.600 m ³ /h
Product family	SVK
Flow rate max. pressure	310.0 l/min

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.05.03.00034