




SVKG G3/8-AG

Check valves SVK, SVKG, SVV are delivered as a ready-to-connect product.

### Technical data

| Attribute | Value   |
|-----------|---------|
| Thread G1 | G3/8"-F |
| Thread G2 | G3/8"-M |



Design data SVKG G3/8-AG

### Design data

| Attribute         | Value    |
|-------------------|----------|
| Length L          | 29.00 mm |
| Thread G1         | G3/8"-F  |
| Thread length LG1 | 12.0 mm  |
| Thread G2         | G3/8"-M  |
| Thread length LG2 | 10.0 mm  |
| Key width SW1     | 22.0 mm  |

Art.-Nr.: 10.05.03.00135

**Technical data**

| Attribute                                      | Value                    |
|------------------------------------------------|--------------------------|
| Weight                                         | 30.3 g                   |
| Required suction capacity for $p_u = -0.3$ bar | 0.440 m <sup>3</sup> /h  |
| Required suction capacity for $p_u = -0.6$ bar | 0.480 m <sup>3</sup> /h  |
| Flow rate max. vacuum                          | 590.0 l/min              |
| Flow rate max.                                 | 35.400 m <sup>3</sup> /h |
| Product family                                 | SVK                      |

**Further documentation**CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.05.03.00135](http://www.schmalz.com/10.05.03.00135)