




DI-PROF 8x14 MOS NK-20 DL

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.

Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	Natural Rubber NK
Width B	8.00 mm
Height H	14.00 mm
Form	with sealing lip



Design data DI-PROF 8x14 MOS NK-20 DL

Design data

Attribute	Value
Width B	8.00 mm
Height H1	7.00 mm
Height H	14.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Sealing profile (meter)

DI-PROF 8x14 MOS NK-20 DL



Art.-Nr.: 10.07.04.00012



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Weight	54.00 g
Sealing material	Natural Rubber NK
Recommended slot width x slot depth [mm]	9x6.5
Product family	DI-PROF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.04.00012



WWW.SCHMALZ.COM/10.07.04.00012