




Technical data

Attribute	Value
Material hose	PU
Bending radius min.	100.0 mm
Color	Milky-transparent
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Outside diameter D	14.00 mm
Internal diameter d	11.00 mm

VSL 14-11 PU MI-TR

Vacuum/compressed air hose VSL is delivered in the desired length.

Available accessories: hose clamp



Design data

Attribute	Value
Outside diameter D	14.00 mm
Internal diameter d	11.00 mm

Design data VSL 14-11 PU MI-TR



Art.-Nr.: 10.07.09.00038

**Technical data**

Attribute	Value
Material hose	PU
Bending radius min.	100.0 mm
Length max.	50.00 m
Pressure range (operating pressure) [bar]	-0.95 ... 10.00 bar
Operating temperature	-20 ... 90 °C
Weight / Meter	0.069 kg/m
Product family	VSL
Design hose type	14-11

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.09.00038

**Ordering Data Accessories 10.07.09.00038**

Type		Item number
Cap (rectangular)	KAPP 9 Band	20.12.01.00036
Hose clamp	SSB 10-16 ST-VZ	10.07.10.00001
Plug union, straight	STV-GE G1/2-AG 14	10.08.02.00300
Plug union, straight	STV-GE G3/8-AG 14	10.08.02.00211
Plug connector, T	SVB-T 14	10.09.02.00046

