




DM 0.5...10 G1/2-IG

Pressure reduction valve DM is delivered as a ready-to-connect product, including mounting bracket.



Design data DM 0.5...10 G1/2-IG

Technical data

Attribute	Value
Flow rate max.	78.000 m ³ /h
Additional function vacuum reservoir	Manometer
Connection	G1/2"-F
Work area [bar]	0,5 ... 10,0

Design data

Attribute	Value
Length L	64.00 mm
Width B1	96.00 mm
Width B2	32.00 mm
Width B	64.00 mm
Height H2	43.50 mm
Height H	135.50 mm
Thread G1	G1/2"-F

Art.-Nr.: 10.07.11.00025



Technical data

Attribute	Value
Weight	0.740 kg
Flow rate max.	78.000 m ³ /h
Operating temperature	-10 ... 60 °C
Work area [bar]	0,5 ... 10,0
Product family	DM
Flow rate max. pressure	1,300.0 l/min



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.11.00025

