

Clamping piece with extension  
**SXT-CL-EXT-A2-125-F25**



Art.-Nr.: 10.07.13.00075




**Technical data**

Material	Aluminum
Outside diameter D	25.00 mm
Internal diameter d	19.00 mm
Connection 1	Bolt with slot Ø19mm
Hole spacing X1	126.0 mm

SXT-CL-EXT-A2-125-F25

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



**Design data**

Length L1	173.50 mm
Length L2	75.00 mm
Length L	165.50 mm
Width B	25.00 mm
Height H1	71.00 mm
Height H2	19.50 mm
Outside diameter D	25.00 mm
Internal diameter d	19.00 mm
Height H3	12.50 mm
Hole spacing X1	126.0 mm

Design data SXT-CL-EXT-A2-125-F25



**Technical data**

Weight	305.00 g
Material	Aluminum
Product family	SXT
Shape	Female



[WWW.SCHMALZ.COM/10.07.13.00075](http://WWW.SCHMALZ.COM/10.07.13.00075)