

Art.-Nr.: 10.07.13.00100

**Technical data**

Attribute	Value
Material	Aluminum
Outside diameter D	40.00 mm
Internal diameter d	25.00 mm
Connection 1	D25
Hole spacing X1	226.0 mm

SXT-CL-EXT-D25-225-F40

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.

**Design data**

Attribute	Value
Length L1	275.00 mm
Length L2	175.00 mm
Length L	274.50 mm
Width B	25.00 mm
Height H1	93.00 mm
Height H2	25.50 mm
Outside diameter D	40.00 mm
Internal diameter d	25.00 mm
Height H3	19.50 mm
Hole spacing X1	226.0 mm

Design data SXT-CL-EXT-D25-225-F40



Clamping piece with extension

SXT-CL-EXT-D25-225-F40



Art.-Nr.: 10.07.13.00100



Technical data

Attribute	Value
Weight	470.00 g
Material	Aluminum
Product family	SXT
Shape	Female



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.13.00100



WWW.SCHMALZ.COM/10.07.13.00100