

Clamping piece with extension
SXT-CL-EXT-A2-250-F40



Art.-Nr.: 10.07.13.00087




Technical data

Material	Aluminum
Outside diameter D	40.00 mm
Internal diameter d	19.00 mm
Connection 1	Bolt with slot Ø19mm
Hole spacing X1	251.0 mm

SXT-CL-EXT-A2-250-F40

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



Design data

Length L1	304.50 mm
Length L2	200.00 mm
Length L	296.50 mm
Width B	25.00 mm
Height H1	83.00 mm
Height H2	25.50 mm
Outside diameter D	40.00 mm
Internal diameter d	19.00 mm
Height H3	12.50 mm
Hole spacing X1	251.0 mm

Design data SXT-CL-EXT-A2-250-F40



Technical data

Weight	480.00 g
Material	Aluminum
Product family	SXT
Shape	Female



WWW.SCHMALZ.COM/10.07.13.00087