

Clamping piece with extension

SXT-CL-EXT-A3-135-F25



Art.-Nr.: 10.07.13.00197




Technical data

Attribute	Value
Material	Aluminum
Outside diameter D	25.00 mm
Internal diameter d	28.50 mm
Connection 1	Ball head 28.5 mm
Hole spacing X1	135.0 mm

SXT-CL-EXT-A3-135-F25

Clamps with extension SXT-CL-EXT are delivered as a ready-to-connect product.



Design data

Attribute	Value
Length L2	75.00 mm
Length L	183.60 mm
Width B	25.00 mm
Height H1	53.00 mm
Height H2	19.50 mm
Height H	57.00 mm
Outside diameter D	25.00 mm
Internal diameter d	28.50 mm
Height H3	23.50 mm
Hole spacing X1	135.0 mm

Design data SXT-CL-EXT-A3-135-F25



WWW.SCHMALZ.COM/10.07.13.00197

Clamping piece with extension

SXT-CL-EXT-A3-135-F25



Art.-Nr.: 10.07.13.00197



Technical data

Attribute	Value
Weight	390.00 g
Material	Aluminum
Product family	SXT
Shape	Female



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.07.13.00197



WWW.SCHMALZ.COM/10.07.13.00197