

Art.-Nr.: 11.02.05.10153




SBM-160-520-IE3-TYP2

Technical data

Attribute	Value
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	43.000 kg
Suction rate (50 Hz)	160.000 m ³ /h
Suction rate (60 Hz)	190.000 m ³ /h
Version	IE3:US/CAN
Approval	UL/CSA
Category	Electrical vacuum generation

Design data

Attribute	Value
Length L	469.00 mm
Width B	370.00 mm
Height H	426.00 mm
Internal diameter d	12.00 mm
Hole spacing X1	290.0 mm



Design data SBM-160-520-IE3-TYP2



Art.-Nr.: 11.02.05.10153



Technical data

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	43.000 kg
Suction rate (50 Hz)	160.000 m ³ /h
Suction rate (60 Hz)	190.000 m ³ /h
Rated power	3.60 W
Version	IE3:US/CAN
Category	Electrical vacuum generation



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/11.02.05.10153

