




SBM-160-520-IE3-TYP4

Technical data

Attribute	Value
Rated power at 50 Hz	3.00 kW
Rated power at 60 Hz	3.60 kW
Voltage at 50 Hz	D290 V / Y500 V ± 10 %
Voltage at 60 Hz	D330 V / Y575 V ± 10 %
Weight	43.000 kg
Suction rate (50 Hz)	160.000 m ³ /h
Suction rate (60 Hz)	190.000 m ³ /h
Sound pressure level at 50 Hz	70.5 dB(A)
Version	IE3:CAN
Approval	UL/CSA
Category	Electrical vacuum generation



Design data SBM-160-520-IE3-TYP4

Design data

Attribute	Value
Length L	469.00 mm
Width B	370.00 mm
Height H	426.00 mm
Internal diameter d	12.00 mm
Hole spacing X1	290.0 mm

Art.-Nr.: 11.02.05.10155

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	3.00 kW
Rated power at 60 Hz	3.60 kW
Voltage at 50 Hz	D290 V / Y500 V ± 10 %
Voltage at 60 Hz	D330 V / Y575 V ± 10 %
Weight	43.000 kg
Suction rate (50 Hz)	160.000 m ³ /h
Suction rate (60 Hz)	190.000 m ³ /h
Sound pressure level at 50 Hz	70.5 dB(A)
Rated power	3.00 W
Version	IE3:CAN
Category	Electrical vacuum generation

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/11.02.05.10155