

WWW.SCHMALZ.COM

Note

This document were originally written in German and have been translated into English.
Store in a safe place for future reference.

Subject to technical changes without notice. No responsibility is taken for printing or other types of errors.

Published by

© J. Schmalz GmbH, 01.2020

This document is protected by copyright. J. Schmalz GmbH retains the rights established thereby. Reproduction of the contents, in full or in part, is only permitted within the limits of the legal provisions of copyright law. Any modifications to or abridgments of the document are prohibited without explicit written agreement from J. Schmalz GmbH.

Contact

J. Schmalz GmbH
Johannes-Schmalz-Str. 1
72293 Glatten, Germany

Tel. +49 (0) 7443 2403-0
Fax +49 (0) 7443 2403-259
schmalz@schmalz.de
www.schmalz.com

Contact information for Schmalz companies and trade partners worldwide can be found at

 www.schmalz.com/salesnetwork

Table of contents

1	Function block “FB_SNGi_AE”	4
1.1	Brief description	4
1.2	Image of function block.....	4
1.3	Parameter - Input.....	5
1.4	Parameter - Output.....	5
2	Appendix	6
2.1	List of abbreviations	6
2.2	Note.....	6


1 Function block "FB_SNGi_AE"

1.1 Brief description

This function block controls the Processdata of Schmalz SNGi AE with IO-Link.

1.2 Image of function block

Example of function block:



1.3 Parameter - Input

name	data type	description
bGoToPosition	BOOL	Needles move to position "btTargetPosition"
bGoToHomePosition	BOOL	Needles move to base (home position)
bMoveEnable	BOOL	Enabling movement of the needle
bCalibration	BOOL	Perform referencing then move to home position
iEPCMode	INT	Request for EPC data can be controlled as following: 0 = no request 1 = request for values of EPC-Select 0 2 = request for values of EPC-Select 1 3 = request for values of EPC-Select 2 4 = request for values of EPC-Select 3 5 = values are automatically picked up
iSetProfile	INT	Choice of desired vacuum profile (0 – 3)
siTargetPosition	SINT	Target position (from 1 = 0,1mm to 200 = 20mm)
siProcessdata_IN1	SINT	Input byte 1 of process data
siProcessdata_IN2	SINT	Input byte 2 of process data
siProcessdata_IN3	SINT	Input byte 3 of process data
siProcessdata_IN4	SINT	Input byte 4 of process data

1.4 Parameter - Output

name	data type	description
bNeedlesInPosition	BOOL	Needles are in selected position
bNeedlesInHomePosition	BOOL	Needles in base (home Position)
bNeedlesMoving	BOOL	Needles in movement
bCalibrationActive	BOOL	Status of the calibration
bDeviceStatus_Green	BOOL	Device is working optimally
bDeviceStatus_Yellow	BOOL	Device is working but there are warnings
bDeviceStatus_Red	BOOL	Device is not working properly
siSpeedOfNeedles	SINT	Speed of needles (%)
iCurrentPositionNeedles	INT	Current position of needles (0,1mm)
siCM_Warnings	SINT	CM Warnings
iSystemTemperature	INT	System temperature (°C)
iTotalMovementTime	INT	Total movement time (s)
siPrimarySupplyVoltage	SINT	Input voltage (V)
iEnergyLastCycle	INT	Energy consumption of last handling cycle (Ws)
siProcessdata_OUT1	SINT	Output byte 1 of process data
siProcessdata_OUT2	SINT	Output byte 2 of process data

2 Appendix

2.1 List of abbreviations

abbreviation	description
FB	Function block
EPC	Energy- and Processcontrol
CM	Condition Monitoring
EM	Energy Monitoring
PM	Predictive Maintenance

2.2 Note

- The byte order of the product is represented as big endian.
- The triggering of the vacuum must be carried out in accordance with the corresponding ejector variant (e.g., NO, NC, IMP).

At your service worldwide



● **Headquarters**
Hauptsitz

Schmalz Germany – Glatten

● **Sales and production companies**
Vertriebs- und Produktionsgesellschaften

Schmalz China – Shanghai
Schmalz India – Pune
Schmalz Japan – Yokohama
Schmalz USA – Raleigh (NC)

● **Sales companies**
Vertriebsgesellschaften

Schmalz Australia – Melbourne
Schmalz Benelux – Hengelo (NL)
Schmalz Canada – Mississauga
Schmalz Finland – Vantaa
Schmalz France – Champs-sur-Marne
Schmalz Italia – Novara
Schmalz Mexiko – Querétaro

Schmalz Poland – Suchy Las (Poznan)
Schmalz Russia – Moskow
Schmalz South Korea – Anyang
Schmalz Spain – Erandio (Vizcaya)
Schmalz Switzerland – Nürensdorf
Schmalz Turkey – Istanbul

• **Sales partners**
Vertriebspartner

You can find the Schmalz sales partner in your country at:
WWW.SCHMALZ.COM/SALESNETWORK

Den Schmalz Vertriebspartner in Ihrem Land finden Sie auf:
WWW.SCHMALZ.COM/VERTRIEBSNETZ

J. Schmalz GmbH
Johannes-Schmalz-Str. 1
72293 Glatten, Germany
T: +49 7443 2403-0
schmalz@schmalz.de
WWW.SCHMALZ.COM

Version 01 | 01.2020