

WWW.SCHMALZ.COM

**Note**

This document were originally written in German and have been translated into English.  
Store in a safe place for future reference.

Subject to technical changes without notice. No responsibility is taken for printing or other types of errors.

**Published by**

© J. Schmalz GmbH, 01.2020

This document is protected by copyright. J. Schmalz GmbH retains the rights established thereby. Reproduction of the contents, in full or in part, is only permitted within the limits of the legal provisions of copyright law. Any modifications to or abridgments of the document are prohibited without explicit written agreement from J. Schmalz GmbH.

**Contact**

J. Schmalz GmbH  
Johannes-Schmalz-Str. 1  
72293 Glatten, Germany

Tel. +49 (0) 7443 2403-0  
Fax +49 (0) 7443 2403-259  
schmalz@schmalz.de  
www.schmalz.com

Contact information for Schmalz companies and trade partners worldwide can be found at

 [www.schmalz.com/salesnetwork](http://www.schmalz.com/salesnetwork)

## Table of contents

1	Function block “FB_SXPi_SXMPi_ClassB” .....	4
1.1	Brief description .....	4
1.2	Image of function block.....	4
1.3	Parameter - Input.....	5
1.4	Parameter - Output.....	6
2	Appendix .....	7
2.1	List of abbreviations .....	7
2.2	Note.....	7


# 1 Function block "FB\_SXPi\_SXMPi\_ClassB"

## 1.1 Brief description

This function block controls the Processdata of Schmalz SXPi/SXMPi Class B with IO-Link.

## 1.2 Image of function block

Example of function block:



### 1.3 Parameter - Input

name	data type	description
bVacuum	BOOL	Request for suction
bBlow_off	BOOL	Request to blow-off
bSettingMode	BOOL	Vacuum on/off with continuous suction disabled
bCM_Autoset	BOOL	Automatic determination and storage in the active profile of max. leakage rate (-L-) and evacuation time (t-1) of last cycle
iEPCMode	INT	Request for EPC data can be controlled as following: 0 = no request 1 = request for values of EPC-Select 0 2 = request for values of EPC-Select 1 3 = request for values of EPC-Select 2 4 = request for values of EPC-Select 3 5 = values are automatically picked up
iSetProfile	INT	Choice of desired vacuum profile (0 – 3)
iInputPressure	INT	Ejectors without a pressure sensor get the input pressure via process data to be able to create EPC analysis. Input size in mbar
bCalibrateSensor	BOOL	Calibration of vacuum sensor and pressure sensor if existing
dwProcessdata_IN	DWORD	Input doubling word of process data

## 1.4 Parameter - Output

name	data type	description
bVacuumControl_H1	BOOL	Control value vacuum
bPartControl_H2	BOOL	Switch-on value signal output „Part control“
bPartDeposited_H3	BOOL	Part deposited
bPressureActivation_HP1	BOOL	Pressure Activation
bCM_AutoSetAck	BOOL	Active when CM Autostart completes successfully
bDeviceStatus_Green	BOOL	Device is working optimally
bDeviceStatus_Yellow	BOOL	Device is working but there are warnings
bDeviceStatus_Orange	BOOL	Device is working but there are severe warnings
bDeviceStatus_Red	BOOL	Device is not working properly
btInputPressure	BYTE	Input pressure (0,1 bar)
wSystemVacuum	WORD	System vacuum (mBar)
btCM_Warnings	BYTE	CM Warnings
wEvacuationTime_t1	WORD	Evacuation time t1 (ms)
btLeakageLastCycle	BYTE	Leakage of last handling cycle (mbar/s)
wLastFreeFlowVacuum	WORD	Last free flow vacuum (mbar)
btPrimarySupplyVoltage	BYTE	Input voltage (V)
wAirConsumptionLastCycle	WORD	Air consumption of last handling cycle (0,1 NL)
wProcessdata_OUT	WORD	Output word of process data

## 2 Appendix

### 2.1 List of abbreviations

abbreviation	description
FB	Function block
EPC	Energy- and Processcontrol
CM	Condition Monitoring
EM	Energy Monitoring
PM	Predictive Maintenance

### 2.2 Note

- The byte order of the product is represented as big endian.
- The triggering of the vacuum must be carried out in accordance with the corresponding ejector variant (e.g., NO, NC, IMP).

## At your service worldwide



● **Headquarters**  
Hauptsitz

Schmalz Germany – Glatten

● **Sales and production companies**  
Vertriebs- und Produktionsgesellschaften

Schmalz China – Shanghai  
Schmalz India – Pune  
Schmalz Japan – Yokohama  
Schmalz USA – Raleigh (NC)

● **Sales companies**  
Vertriebsgesellschaften

Schmalz Australia – Melbourne  
Schmalz Benelux – Hengelo (NL)  
Schmalz Canada – Mississauga  
Schmalz Finland – Vantaa  
Schmalz France – Champs-sur-Marne  
Schmalz Italia – Novara  
Schmalz Mexiko – Querétaro

Schmalz Poland – Suchy Las (Poznan)  
Schmalz Russia – Moskow  
Schmalz South Korea – Anyang  
Schmalz Spain – Erandio (Vizcaya)  
Schmalz Switzerland – Nürensdorf  
Schmalz Turkey – Istanbul

• **Sales partners**  
Vertriebspartner

You can find the Schmalz sales partner in your country at:  
**WWW.SCHMALZ.COM/SALESNETWORK**

Den Schmalz Vertriebspartner in Ihrem Land finden Sie auf:  
**WWW.SCHMALZ.COM/VERTRIEBSNETZ**

**J. Schmalz GmbH**  
Johannes-Schmalz-Str. 1  
72293 Glatten, Germany  
T: +49 7443 2403-0  
schmalz@schmalz.de  
WWW.SCHMALZ.COM

Version 01 | 01.2020