



PalPharmaMove™

CGMP Fixed and Mobile Lifting and Handling Systems

Streamline lifting and handling operations with PalPharmaMove™ systems. Whether manual or powered, these systems offer versatility and efficiency, designed to fit through standard doorways and accommodate various materials with ease.

Product information

Typical applications:

- ✓ Manual push/pull M3/M5/M7 or powered drive K9 versions available
- ✓ Can be battery, electric or pneumatic – No hydraulics are used ever
- ✓ PLC control system – K9
- ✓ Suitable for ATEX environment to zone 1/2T4 with documentation (pneumatic)
- ✓ Optional telescopic mast to achieve 3.2m lift height but can still fit through a 2.1m doorway height
- ✓ Stacker/Straddle Base M7 5kg (11lb) – 1 tonne (2200lb) capacity
- ✓ Counterbalanced K9 version – 1500kg (3300lb) capacity. Higher capacity on application
- ✓ Compact footprint which is designed to fit through standard doorways
- ✓ Effortless to move



FORMERLY  Palamatic



M3

Mobile trolley with manual handwheel raise and lower for simple transport, docking and lifting tasks




M5

Fixed mast manually propelled mobile truck with manually actuated drum raise, lower and forward pour



M7

Fixed mast manually propelled mobile truck with pneumatically actuated drum raise, lower and forward pour



K9

Electrically propelled mobile truck for gripping lifting and inverting drums and IBC's, Bins and Totes up to 250kg



Why Trust Palamatic For Quality Material Handling Equipment?

Rely on Palamatic for top-tier material handling equipment and an unwavering commitment to quality and innovation. With a track record of delivering exceptional solutions, we stand out as a trusted provider in the industry.



Est. in 1985

Over 35 Years in Business



10,000+

Projects Completed



50+ Countries

Operating Worldwide

Service Plan

Ask a member of our team about the Palamatic flexible service plan.

Different levels of regular servicing are available, dependent upon your requirements.